

Technical data sheet V100K

Specification Four legged, not upholstered, Plastic shell

Dimensions in mm	Backrest:	H:	420	
		Seat:	H:	435
			W:	445
			D:	415
	Total:	H:	820	
		W (no ArmR):	510	
D:		565		
Packaging data	Weight:	kg	5,7	
	Volume:	m³	0,37	



Basic equipment

Benefit

Seat and Backrest	Seat and backrest made of plastic ergonomically-formed, backrest height 290 mm.	
Frame	Chrome-plated frame with elliptically-shaped steel tube. 30 x 15 x 2 mm. Technically patented.	Very high stability, longevity. High-quality look.
Stackability	Stacking height of the vertical stacking: 20 chairs.	Space-saving storage.
Plastic parts	White. Highly durable 2-component shell. Polypropelene with fibreglass core.	Very high stability, longevity. High-quality look.
Glides	Plastic glides for soft floors, black.	Optimum stability of the chair. Protection of the floor.
Materials	All materials are segregated and recyclable.	Environmentally friendly.
Standards	DIN EN 16139 four leg and chantilever. GS-symbol for tested safety, tested for contaminants.	High safety and comfort.
Certification	Quality management system DIN EN ISO 9001:2008, VO (EG) No. 1221/2009 (EMAS), Environmental management system DIN EN ISO 14001:2009, OHSAS, EcoVadis gold, Commitment to sustainability. Blue Angel.	High-quality product.
Warranty and return	10 years warranty. Complete return and recycling guarantee.	Exchange of parts, free of charge, within the guaranteed period.

Disassembly instructions are available upon request for any interstuhl product

Technical data sheet V100K

Specification Four legged, not upholstered, Plastic shell

Dimensions in mm	Backrest:	H:	420	
		Seat:	H:	435
			W:	445
			D:	415
	Total:	H:	820	
		W (no ArmR):	510	
D:		565		
Packaging data	Weight:	kg	5,7	
	Volume:	m³	0,37	



Options		Benefit
Plastic parts	Anthracite, light grey.	Optical design variety.
Glides	Felt glides for hard floors, black.	Optimum stability of the chair. Protection of the floor.
Armrests/Accessories	Armrests with plastic pad, row connector, panic bolt.	Optimal function extension depending on individual usage.

Disassembly instructions are available upon request for any interstuhl product